

101ppm Low Dew Point Instrument Air Dryer Package System With Analyzer

Basic Information

Place of Origin: CHINA
Brand Name: GASPU
Certification: CE
Model Number: UAD
Minimum Order Quantity: 1set
Price: Negotiate

Packaging Details: Plywood or other type

• Delivery Time: 75work days

Payment Terms: T/T

Supply Ability: 4set/month



Product Specification

Material: CS Or SS
Standard: GB150/ASME
Capacity: 1-85m3/min
Dew Point: Below-40

Process: Heatless And FreezePower: 110-230V 50Hz 0.2kw

Color: CustomizableWork Pressure: 5-13barg

• Highlight: 101ppm instrument air dryer package,

 $\label{low-point} \mbox{Low Point instrument air dryer package},$

101ppm instrument air dryer system



Product Description

Low dew point Air Dryer With analyzer

Compressed air first go into first air filter to remove large amount of liquid water, then go into sencond filter to remove oil and dust, then compressed air go into heatless air dryer to remove wate deeply. After filter will remove dust in air which precision reach 0.01um.

At outlet of air dryer, dew point will be reach 101ppm (option 2.9ppm).

The heatless regeneration adsorption dryer is a device that uses the principle of pressure swing adsorption to dry compressed air. It mainly adsorbs water from compressed air by filling with adsorbents such as alumina or molecular sieves with high water absorption, thereby achieving the purpose of drying. In this process, the heat free regeneration adsorption dryer does not require an external heat source. Instead, it reduces the pressure of the adsorbent bed to allow the water adsorbed on the adsorbent to desorb, achieving the regeneration of the adsorbent.

Datasheet

Item	Specification
Product	Combination Air Dryer With Freeze Dryer
Usage Life	20 years
Dew point	101ppm(Option2.9ppm)
Movable	YES
Air Compressor	Option
Capacity4	10-600SCFM
Status	for IA product
Payment	Discussed
Service Life	20Years
Inlet Pressure	6.5-13barg

Technical characteristics

- 1. Energy saving: Due to that the heatless regeneration adsorption dryer does not require an external heat source, its energy consumption is lower compared to dryers that require heating regeneration.
- 2. Environmental protection: The heat free regeneration adsorption dryer does not produce any pollutants during the drying process and meets environmental protection requirements.
- 3. Stable outlet dew point: The heatless regeneration adsorption dryer can dry compressed air to a dew point of -40 to -70, meeting the needs of various industrial applications.
- 4. Easy to maintain: The structure of the heat free regeneration adsorption dryer is relatively simple, making maintenance more convenient.
- 5. Wide application areas: Heatless regeneration adsorption dryers are widely used in industrial fields that require compressed air drying, such as electronics, food, chemical, and medicine.

matters needing attention

The equipment should be installed in a well-ventilated, dry and clean environment.

Regular maintenance and upkeep of equipment, including replacing adsorbents, clean or replacing filters, etc.

Operate and use according to equipment requirements to avoid equipment damage or safety accidents caused by mis operation or overload operation.

Regularly inspect the export dew point of the equipment to ensure that it meets the requirements of industrial applications.

GASPU can provide heatless regeneration dryers with a production capacity of 1-85m3/min and a dew point between -40 and -70 . The standard pressure vessel for conventional products is GB150/ASME, and various customized designs can be made according to the actual needs of users.









No.161 Zhongfeng Street, Suzhou New District, Suzhou, P.R.China